

VESTAKEEP® DC4470 G



Gingiva-colored polyether ether ketone for dental applications

VESTAKEEP® DC4470 G is a gingiva-colored, high viscosity polyether ether ketone (PEEK) resin that is especially designed for removable dentures to meet the aesthetic demands of the patient.

For VESTAKEEP® DC4470 G, biocompatibility has been tested according to ISO 10993-1 recommendations for permanent mucous membrane contact.

The compound composition is optimised for high biocompatibility and superior mechanical, thermal and chemical resistance.

VESTAKEEP® DC4470 G can be processed by common melt processing techniques like injection molding and extrusion.

For injection molding, we recommend a melt temperature in the 380°C to 400°C range. The mold temperature should be within 160°C to 200°C, preferably 180°C.

VESTAKEEP® DC4470 G is supplied as cylindrical pellets in 25kg boxes with polyethylene liners.

Biocompatibility test reports available for DC4470 G

Standard	Description
ISO10993-03	Genotoxicity: Salmonella Typhimurium Reverse Mutation Test (Ames Test)
ISO 10993-05	Cytotoxicity: Quantitative Growth Inhibition Test
ISO 10993-10	Irritation: Intracutaneous Reactivity
ISO 10993-10	Sensitization: Local Lymph Node Assay
ISO 10993-11	Acute Systemic Toxicity
ISO 10993-11	Subacute / Subchronic Toxicity 14 days
ISO 10993-18	Extraction Tests
USP Class VI	Acute Systemic Toxicity Intracutaneous Reactivity Muscle Implantation

For further information, please contact us at evonik-hp@evonik.com.

Properties of VESTAKEEP® DC4470 G

Properties		Test method	Unit	Value
Density	23°C	ISO 1183	g/cm ³	1.36
Tensile test	23°C / 50% r.h.	ISO 527-1 ISO 527-2		
Stress at yield			MPa	95
Strain at yield			%	5.0
Strain at break			%	> 10
Tensile modulus		ISO 527-1 ISO 527-2	MPa	3600
CHARPY impact strength	23°C / 50% r.h.	ISO 179/1eU	kJ/m ²	N ¹⁾
CHARPY notched impact strength	23°C / 50% r.h.	ISO 179/1eA	kJ/m ²	7.5 C ¹⁾
Temperature of deflection under load				
Method A	1.8 MPa	ISO 75-1	°C	155
Method B	0.45 MPa	ISO 75-2	°C	210
Vicat softening temperature		ISO 306		
Method A	10N		°C	335
Method B	50N		°C	305
Linear thermal expansion longitudinal	23-55°C	ISO 11359	10 ⁻⁴ K ⁻¹	0.45
Melting range DSC	2 nd heating	ISO 11357	°C	approx. 340
Melt volume-flow rate (MVR)	380°C/5kg	ISO 1133	cm ³ /10min	11
Water absorption	saturation	ISO 62	%	0.4

¹⁾ C = Complete break, incl. hinge break H
N = No break

VESTAKEEP® is a registered trademark of Evonik Degussa GmbH

This information and any recommendations, technical or otherwise, are presented in good faith and believed to be correct as of the date prepared. Recipients of this information and recommendations must make their own determination as to its suitability for their purposes. In no event shall Evonik assume liability for damages or losses of any kind or nature that result from the use of or reliance upon this information and recommendations. EVONIK EXPRESSLY DISCLAIMS ANY REPRESENTATIONS AND WARRANTIES OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO THE ACCURACY, COMPLETENESS, NON-INFRINGEMENT, MERCHANTABILITY AND/OR FITNESS FOR A PARTICULAR PURPOSE (EVEN IF EVONIK IS AWARE OF SUCH PURPOSE) WITH RESPECT TO ANY INFORMATION AND RECOMMENDATIONS PROVIDED. Reference to any trade names used by other companies is neither a recommendation nor an endorsement of the corresponding product, and does not imply that similar products could not be used. Evonik reserves the right to make any changes to the information and/or recommendations at any time, without prior or subsequent notice.

Evonik Resource Efficiency GmbH

Paul-Baumann-Str.1, 45772 Marl

Phone +49 2365 49-9227 e-mail evonik-hp@evonik.com

www.vestakeep.com